



Internal Halogen-quenched, uncompensated GM tube with thin mica window, 1.4-2.0 mg/cm2 areal density. Effective diameter of window is 45 mm (1.77 in.).

Averaging Periods

Display will update every 3 seconds. At low background levels, the update is the moving average for the past 30-second time period. The timed period for the moving average decreases as the radiation level increases.

Operating Range

mR/hr - .001 (1 μ R) to 100 CPM - 0 to 350,000 μ Sv/hr - .01 to 1000 CPS - 0 to 5000 Timed Count - 1 to 9,999K (9,999,000) counts

Accuracy

(Referenced to Cs137) Typically ±15% from factory, ±10% with NIST Source Calibration

Size

140 X 68 X 33 mm (5.5 X 2.7 X 1.3 in.)


Energy Sensitivity

3340 CPM/mR/hr referenced to Cs¹³⁷

- Detects Alpha down to 2 MeV.
- Detects Beta down to .16 MeV; typical detection efficiency at 1 MeV is approx. 25%.
- Detects Gamma down to 10 KeV through the end window. Smallest detectable level for I¹²⁵ is .02 uCi at contact.

Built-In Efficiencies

³⁵Sulfur (S35), ⁹⁰Strontium (Sr/y90), ¹³⁷Cesium (Cs137), ³²Phosphorus (P32), ¹⁴Carbon (C14), ¹³¹Iodine (I131), ⁶⁰Cobalt (Co60), and Alpha



元翔五金行 電話:04-22615775 傳真:04-22621395

住址:台中市復興路二段120之19號 http://yuansum.myweb.hinet.net



Display

Backlit Graphic LCD with Backlight

Count Light

Red LED flashes with each radiation event

Alert Set Range

mR/hr .001 - 100 and CPM 1 - 350,000

Alarm Indicator

Internal beeper. 70db @ 1m. (can be switched off for silent operation)

Outputs

USB for use with Observer USB Software Family

Anti-Saturation

Meter will hold at full scale in fields as high as 100 times the maximum reading.

Battery Door on Back

Power Requirements

Two AA alkaline batteries. Approx. 800 hrs @ background.

Includes

Carrying Case, Xtreme Boot, Stand, Detector Cover, Lanyard, Mini-USB Cable, Observer USB Software Download, Certificate of Conformance


Options


Wipe Test Plate, Swipes, NIST Calibration

Warranty

1 year limited







USB Observer Software collects data stored in the internal memory of The Radiation Alert Ranger





Optional Wipe Test Plate Shown

元翔五金行 電話:04-22615775 傳真:04-22621395

住址:台中市復興路二段120之19號 http://yuansum.myweb.hinet.net